

Product leaflet

Product
Half mask

Model No.
SR 100 M/L, S/M

Ordering No.
H01-2012, H01-2112

Product Description

The SR 100 half mask is made of silicone in two sizes, i.e. S/M and M/L. The mask is equipped with two exhalation valves, which ensures very low exhalation resistance. The valve covers with partitions effectively protect the exhalation membrane against dust and paint mist. The material and pigment of the mask body are approved by FDA and BGA for foods, which minimizes the risk of contact allergies. The easily adjustable elastic head harness straps of the mask are designed as a V-shaped loop and have a large dished crown plate, which contributes towards a comfortable and safe fit. The mask is used either as a filtering device in combination with filters from the Sundström range, or in combination with the SR 307 compressed air attachment which then serves as a breathing apparatus with continuous flow for connection to a compressed air supply.


A pre-filter holder and test disc for simple checking of the performance are supplied. Best stored in box SR 230 or storage case SR 339.

Technical specification

	SR 100	EN 140:1998
Protection factor ¹	20	-
Inhalation resistance at 30 l/min	≈ 3 Pa	≤ 50 Pa
Exhalation resistance at 160 l/min	≈ 70 Pa	≤ 300 Pa
Service temperature	-10 – +55 °C, < 90 % RH	-
Storage temperature	-20 – +40 °C, < 90 % RH	-
Weight	≈ 179 g	-
Approval	EN 140:1998	-

1) Specified in BS 4275, and applies generally to all half masks with particle filters P3, regardless of the test results.

- A. Mask body
- B. Filter attachment
- C. Head harness straps
- D. Exhalation valve seat
- E. Exhalation membrane
- F. Inhalation valve seat
- G. Inhalation membrane
- H. Protective cap
- I. Filters (not included)
- J. Pre-filter (not included)
- K. Pre-filter holder



Head Office

Tel: +46-(0)8-562 370 00
Fax: +46-(0)8-562 370 20

P.O. Box 10056
SE-181 10 Lidingö
Sweden

Visiting address:
Vasavägen 84
SE-181 10 Lidingö

Factory

Tel: +46-(0)8-562 370 00
Fax: +46-(0)8-562 370 60

P.O. Box 76
SE-340 14 Lagan
Sweden

Visiting address:
Västergatan 4
SE-340 14 Lagan

Sundström 
www.srsafety.se